

# Absorbtion Of SiON Waveguides

**File name:** SiON\_waveguide.apc

**Reference:** K. Worhoff, P. V. Lambeck and A. Driessen, “*Design, Tolerance Analysis and Fabrication of Silicon Oxynitride Based Planar Optical Waveguides for Communication Devices*”, *Jornal of Lightwave Technol.*, Vol. 17, No. 8, pp. 1401-1407, August 1999.

This example shows how external data can be used to define variables, and how a variable can be expressed as a function of another one.

Silicon Oxinitride is an excellent material for the realization of medium contrast planar integrated optics circuits. However, due to the unavoidable N-H bounds presents in the material, a peak absorption around a wavelength of 1510 nm can impact on the performance of the circuit. The bell shaped absorption depends on the index contrast  $\Delta n$ , on the technological process (annealing, deuterated material, etc.) and on the dimension of the waveguide and can be modelled with the following fitting formula

$$\alpha = \frac{(A-D)}{2} \left[ \frac{1}{1+B(\lambda-\lambda_{p1})^2} + \exp\left(-\frac{(\lambda-\lambda_{p2})^2}{C}\right) \right] + D \quad \text{dB/cm}$$

where  $\lambda_{p1}$  and  $\lambda_{p2}$  are the peak absorption wavelengths respectively due to the Lorentzian and the Gaussian contributes, A is the peak absorption, B and C define the width of the absorption peak and D is the material loss contribute far away from the absorption peak.

Some example of coefficient derived from measured spectral attenuations are

$\Delta n=2.5\%$  index contrast SiON waveguide with an attenuation peak of 0.45 dB/cm at the wavelength  $\lambda_p=1506$  nm is described by  $A=0.45$ ,  $B=3000$ ,  $C=0.000504135$ ,  $\lambda_{p1}=1.50616$ ,  $\lambda_{p2}=1.50569$  and  $D=0.0211103$ ;

$\Delta n=6.0\%$  index contrast SiON waveguide with an attenuation peak of 3.48 dB/cm at the wavelength  $\lambda_p=1507$  nm is described by  $A=3.48$ ,  $B=3000$ ,  $C=0.000298746$ ,  $\lambda_{p1}=1.50534$ ,  $\lambda_{p2}=1.50763$  and  $D=0.01$ ;

In this example a simple straight waveguide realized in SiON technology with an index contrast of 6% is analysed. The measured attenuation of the waveguide is read from the data file `Absorbtion_SiON60.txt` and used in the simulation. The ‘Variables’ panel and in Parameter panel of the straight waveguide the definition of the attenuation is clearly visible.

Fig. 1 show the spectral insertion loss of a 1cm long waveguide. ASPIC interpolates and extrapolates data where missing. The second straight waveguide uses the above fitting formula to calculate waveguide losses and figure 1 shows both spectral behaviours, superimposed. The agreement is fairly good.

An example of the impact of such a wavelength dependence on a single ring resonator filter is shown in Fig. 2. Note that around the absorption peak the extinction ratio reduces and the bandwidth increases because of a higher absorption.




Fig. 1 – Spectral insertion loss of a SiON waveguide. In blue the measured data; in green the fitted behaviour




Fig. 2 – Spectral behaviour of a lossy ring resonator